



Micrometer

Selection chart:

Model	Travel range(mm)	Minimum reading(mm)	Screw pitch(mm)	Weight	Installation dimension(mm)
J-MHF2-13	Coarse adjustment: 13	Coarse adjustment: 0.01	Coarse adjustment: 0.5	0.1	$\Phi 9.5 \times 11$
	Fine adjustment: 0.2	Fine adjustment: 0.0005	Fine adjustment: 0.025		
J-MHF2-13F	Coarse adjustment: 13	Coarse adjustment: 0.01	Coarse adjustment: 0.5	0.1	$\Phi 9.5 \times 5.5$
	Fine adjustment: 0.2	Fine adjustment: 0.0005	Fine adjustment: 0.025		
CF2-13F	Coarse adjustment: 13	Coarse adjustment: 0.01	Coarse adjustment: 0.5	0.1	$\Phi 9.5 \times 5.5$
	Fine adjustment: 0.2	Fine adjustment: 0.0005	Fine adjustment: 0.025		




ACSM series micrometer. Standard micrometer pitch 0.5mm, minimum reading 0.01mm:

Selection chart:

Model	End surface type	Effective travel range	Pitch(mm)	Diameter for installation(mm)	Length for installation(mm)	Overall length(mm)
ACSM25-1	Flat	25	0.5	$\Phi 11$	16.5	97
ACSM25-2	Spherical	25	0.5	$\Phi 11$	16.5	99.6

ACSM25-1



ACSM25-2

