

PHVP series Translating Post Holder


PHVP-1/PHVP-2 Translating Post



Brief Introduction:

When adjusting the optical path, if only the height of the post needs slight modification without changing the angle, PHVP series lifting rod seat would be a perfect option.

First, fix the post holder at the selected position in the optical path, insert the post into the center hole of the lifting post holder, and use the post locking handwheel to lock it after roughly adjusting the height. Adjust the lifting part to the expected height, and lock it with the lifting part locking handwheel, and the adjustment is completed.




Model	PHVP-1	PHVP-2
Overall Height(mm)	72~87	95~120
Fine Tuning Height(mm)	15	25
Net Weight(Kg)	0.1	0.15

PHVP-3 Translating Post Holder



Brief Introduction:

This product features a height fine-adjustment function, and the precision-machined lifting thread brings you a comfortable feeling. The standard threaded hole on the top of the center lifting rod can be connected to a variety of related products, which has strong adaptability.




Related Products:

PHSP12 series Post
BPMB series Magnet Base


Specifications:

Fine Tuning Range: 50 mm
Net Weight: 0.6Kg



PHPB-1 Holder Base



PHAF Clamping Fork



PHSP12C Mounting Clamp For Post



Related Products:

PHSP12 series Post