

Fiber Optical Visible Light Combiner

(2 or 3 wavelengths)



DATASHEET

BUY NOW



Features

- Wavelength Independent
- Ultra Low Excess Loss
- Low Polarization Sensitivity
- Highly Stable & Reliable
- Ultra Low Cost

Applications

- Telecommunications
- CATV
- Local Access Network (LAN)
- Fiberoptic Instrumentation

The LFC Series fiber optical visible light combiners are based on Agiltron's fused biconical taper technology and compact packaging structure. They enable any two or three primary colors in the visible wavelength region to be combined or separated. Configurations are available for full RGB colors of red/green/blue. It features good uniformity, low excess loss and very low polarization sensitivity.

Couplers are highly efficient in splitting light with little loss, about 0.2dB per joint, but incur significant losses when combining lights; for example, a 50/50 coupler produces a 50% loss to each beam when combined. For beam-combining applications, search Combiner.

Specifications

Parameter	Min	Typical	Max	Unit
Operation Wavelength	970 ~ 990 / 1535 ~ 1565			nm
Insertion Loss ^[1]		< 0.2		dB
Temperature Dependent Loss		< 0.1		dB
Wavelength Dependent Loss		< 0.15		dB
Isolation		> 20		dB
Polarization Dependent Loss		< 0.1		dB
Return Loss		> 50		dB
Directivity		> 55		dB
Optical Power Handling		< 4		W
Operating Temperature	-10		70	°C
Storage Temperature	-40		85	°C
Fiber Type	HI1060 or HI980			
Package Dimension	(f)3.0 x (L)54			mm

Notes:

[1]. Excluding connectors

Note: The specifications provided are for general applications with a cost-effective approach. If you need to narrow or expand the tolerance, coverage, limit, or qualifications, please [click this link](#):



Legal notices: All product information is believed to be accurate and is subject to change without notice. Information contained herein shall legally bind Agiltron only if it is specifically incorporated into the terms and conditions of a sales agreement. Some specific combinations of options may not be available. The user assumes all risks and liability whatsoever in connection with the use of a product or its application.

Rev 05/27/24

© Photonwares Corporation

P +1 781-935-1200

E sales@photonwares.com

W www.agiltron.com

Information contained herein is deemed to be reliable and accurate as of the issue date. Photonwares reserves the right to change the design or specifications at any time without notice. Agiltron is a registered trademark of Photonwares Corporation in the U.S. and other countries.

Fiber Optical Visible Light Combiner

(2 or 3 wavelengths)



DATASHEET

Ordering Information (Part Number)

	☐	☐	☐	☐	1	☐	☐	☐
Prefix	Type	Color 1	Color 2	Color 3	Coupling Ratio	Port	Fiber Type	Connector ^[1]
LFC-	Two Colors = 2 Three Colors = 3	Red = 1 Green = 2 Blue = 3	Red = 1 Green = 2 Blue = 3	Red = 1 Green = 2 Blue = 3		1x2 = 1 1x3 = 3 Special = 0	Special = 0	None = 1 FC/PC = 2 FC/APC = 3 SC/PC = 4 SC/APC = 5 ST/PC = 6 LC/PC = 7 LC/APC = A LC/UPC = U Special = 0

[1]. The default connector configuration uses fiber with 0.9 mm buffer protection. The connector cannot be installed directly onto bare fiber because the bare fiber is prone to damage during shipping. However, the connector can be assembled on bare fiber if a 3 cm protective loose tube is added for reinforcement. The customer may remove this protective tube after testing. The optical power handling of a standard connector is less than 0.5 W for SMF-28 fiber and decreases further for smaller-core fibers.

Application Notes

Fiber Core Alignment

Note that the minimum attenuation for these devices depends on excellent core-to-core alignment when the connectors are mated. This is crucial for shorter wavelengths with smaller fiber core diameters that can increase the loss of many decibels above the specification if they are not perfectly aligned. Different vendors' connectors may not mate well with each other, especially for angled APC.

Fiber Cleanliness

Fibers with smaller core diameters ($<5 \mu\text{m}$) must be kept extremely clean, contamination at fiber-fiber interfaces, combined with the high optical power density, can lead to significant optical damage. This type of damage usually requires re-polishing or replacement of the connector.

Maximum Optical Input Power

Due to their small fiber core diameters for short wavelength and high photon energies, the damage thresholds for device is substantially reduced than the common 1550nm fiber. To avoid damage to the exposed fiber end faces and internal components, the optical input power should never exceed 20 mW for wavelengths shorter 650nm. We produce a special version to increase the how handling by expanding the core side at the fiber ends.