

Laser Diode/TEC Controllers—Module



up to 10A laser current, constant current/power mode, up to 2A TEC current, ultra-stable feedback control

DATASHEET

[Return to the Webpage](#)



The Agiltron LDCM series laser source module is designed for OEM applications, featuring all-in-one high reliability and highly stable laser output. The LDCM contains high-precision, low-noise, auto-feedback laser diode drive electronics to ensure constant output power or constant driving current, along with an integrated temperature controller that maintains optimal operating conditions. An optional fiber optical isolator can be integrated to prevent reflection-induced laser emission instability, which is essential for achieving highly stable lasers. Agiltron produces isolators from 370nm to 2600nm. The system provides up to 1A driving current and up to 2A TEC cooling current. Each unit features a single FC/APC connector output and two front rotating knobs for independent setting of laser output power and temperature. A toggle switch allows selection between constant current control mode and feedback constant output power mode.

Features

- All-In-One Compact Format
- Easy to User
- LD Current up to 1A
- Compatible with All Laser Types
- Adjustable Laser Diode Current
- Constant Current or Constant Power
- Ultra-Stable Feedback Control

Applications

- Laser Modules
- Laboratory Use
- Systems



Laser Safety

This product meets the appropriate standard in Title 21 of the Code of Federal Regulations (CFR). FDA/CDRH Class 1M laser product. This device has been classified with the FDA/CDRH under accession number 0220191. All versions of this laser are Class 1M laser products, tested according to IEC 60825-1:2007 / EN 60825-1:2007. An additional warning for Class 1M laser products. For diverging beams, this warning shall state that viewing the laser output with certain optical instruments (for example eye loupes, magnifiers, and microscopes) within a distance of 100 mm may pose an eye hazard. For collimated beams, this warning shall state that viewing the laser output with certain instruments designed for use at a distance (for example telescopes and binoculars) may pose an eye hazard.

Wavelength = 1.3/1.5 μ m. Maximum power = 30 mW.

Rev 06/10/26

Specifications

Parameter		Min	Typical	Max	Unit
Output Laser Control Current			1	5	A
Noise Ripple			150	180	μ A RMS
Stability ^[1]	1hr	0.08			%
	24hr	0.04			
Slow Start Ramp		15			mA/msec
External Modulation Bandwidth ^[1]		DC		500	kHz
External Modulation Depth ^[2]		97			%
External Modulation Rise/Fall ^[3]		300		-	ns
Power Supply Voltage		4.5	5	6	V
Power Supply Current			6	25	A
Internal Power Dissipation ^[4]			2	5	W
Operating Temperature		-40		80	°C
Storage Temperature		-60		85	°C
TEC Control Current				2.2	A
Lase Temperature Stability ^[4]		0.02		0.3	°C

Notes:

- [1] Constant current
- [2] 100kHz sine wave
- [3] laser current 500 mA
- [4] 25°C



+1 781-935-1200

sales@agiltron.com

www.agiltron.com

Information contained herein is deemed to be reliable and accurate as of the issue date. We reserve the right to change the design or specifications at any time without notice.
Agiltron is a registered trademark of Optowares Corporation in the U.S. and other countries.


Laser Diode/TEC Controllers–Module



up to 10A laser current, constant current/power mode, up to 2A TEC current, ultra-stable feedback control

DATASHEET

Mechanical Dimensions (mm)



*Product dimensions may change without notice. This is sometimes required for non-standard specifications.

P +1 781-935-1200

E sales@agiltron.com

W www.agiltron.com

Information contained herein is deemed to be reliable and accurate as of the issue date. We reserve the right to change the design or specifications at any time without notice.
Agiltron is a registered trademark of Optowares Corporation in the U.S. and other countries.

Laser Diode/TEC Controllers–Module



up to 10A laser current, constant current/power mode, up to 2A TEC current, ultra-stable feedback control

DATASHEET

Operation Manual

- Connect to the accompanied power supply
- Turn on the power switch
- Laser light should be out with manufacturing settings meeting the part number specifications
- To adjust the settings, follows the manual that is downloadable

Ordering Information (Part Number)

	☐	☐	☐	☐	2	☐	☐
Prefix	Configuration	Laser Current	TEC Current	Type	Package	Power Supply	Laser Mount
LDCM-	Standard = 1 Special = 0	1A = 1 3A = 3 5A = 5	2.2A = 1 Special = 0	Standard = 11 Special = 00	Standard = 2 Special = 0	Non = 22 Yes = 11	Non = N TOCAN A = 1 Butterfly A = 2 Butterfly B = 3 Butterfly C = 4 TOCAN B = 5

Red is non-standard specially made at a higher cost

Caution Extremely Electrostatic Sensitivity



- Never touch laser diode and the module using hands
- Always use protections when handle a laser diode
- Recommend mounting the laser diode using an ionic gun and ESD finger cots



+1 781-935-1200

sales@agiltron.com

www.agiltron.com

Information contained herein is deemed to be reliable and accurate as of the issue date. We reserve the right to change the design or specifications at any time without notice.
Agiltron is a registered trademark of Optowares Corporation in the U.S. and other countries.


Laser Diode/TEC Controllers–Module



up to 10A laser current, constant current/power mode, up to 2A TEC current, ultra-stable feedback control

DATASHEET

Typical Laser Output Stability (butterfly package with temperature control)



P +1 781-935-1200

E sales@agiltron.com

W www.agiltron.com

Information contained herein is deemed to be reliable and accurate as of the issue date. We reserve the right to change the design or specifications at any time without notice.
Agiltron is a registered trademark of Optowares Corporation in the U.S. and other countries.