


NanoSpeed™ Switchable Fiber Optical Splitter/Coupler

(1x2, 2x2, SM, PM, Bidirectional)



DATASHEET

[Return to the Webpage](#)



Features

- High Speed
- High Reliability
- Low Loss
- Temperature Stable
- Compact

Applications

- Instrumentation
- Power balance
- Sensor

The Switchable Fiber Optical Splitter in 1x2 format splits an incoming optical signal into two output optical fibers with the capability of switching between two splitting ratios. The initial split ratio should be predefined in design, while the second split ratio will be preset in delivery. When the control signal is low (<0.8V), the splitter sustains an initial ratio. When applying the high control voltage (3~5V), the splitting ratio will be switched from the initial ratio to the secondary one. The device is bidirectional, transmitting light in both directions simultaneously. In the 2x2 format, the input light from two inputs will be split into two outputs in a similar way of the 1x2 format, but the splitting ratio is reversed each other between two input lights. The switchable Fiber Optic Splitter has passed Telcordia reliability qualification tests as well as aerospace qualifications. It is designed to meet the most demanding ultra-high reliability requirements, fast response time, and continuous operation. The switch is intrinsically bidirectional and selectable for polarization-independent or polarization-maintain by the fiber type.

The unit is mounted on a driving board having a control signal input SMC connector and a wall plug-in power supply. Available with several drivers having performance optimized for various repetition rates.

The rise/fall time is intrinsically related to the crystal properties, and the repetition rate is associated with the driver. There are poor frequency response sections due to the device resonances. The NS devices are shipped mounted on a tuned driver.

The NS series switches respond to a control signal with any arbitrary timing with frequency from DC up to MHz. The switch is usually mounted on a tuned driver before shipping. The electrical power consumption is related to the repetition rate at which the switch is operated.

The dual-stage configuration increases the extinction ratio or cross-talk value.

Specifications

Parameter		Min	Typical	Max	Unit
Central Wavelength		450		2000	nm
	1260~1650nm		0.8	1.8	dB
Insertion Loss ^[1]	900~1260nm		0.6	1.0	dB
	760~900nm		0.8	1.3	dB
	650~850nm		1.2	1.5	dB
	450~580nm		1.5	2.3	dB
Cross Talk at 100% splitter ^[2]		20	25	35	dB
Durability		10 ¹⁴			cycles
Splitting ratio ^[3]	Initial	0		100	%
	Switching	0		100	%
	Type	Continuous			
Response Time (Rise, Fall)				1000	ns
Repetition Rate ^[4]		DC		500	kHz
Polarization Dependent Loss			0.1	0.35	dB
IL Temperature Dependency			0.25	0.5	dB
Polarization Mode Dispersion			0.1	0.2	Ps
Return Loss		45	50	60	dB
Operating Temperature		-5		70	°C
Optical Power Handling ^[5]			0.3	20	W
Storage Temperature		-40		85	°C

Notes:

[1] Excluding connectors.

[2] ± 25nm, Cross talk is measured at 5kHz, which may be degraded at the high repeat rate.

[3] The initial ratio must be predefined. The switching ratio will be preset in delivery.

[4] High repetition rate (up to 1MHz) is available in the premium version, please contact us.

[5] Defined at 1310/1550nm. For the shorter wavelength, the handling power may be reduced.

Warning: This is an OEM module designed for system integration. Do not touch the PCB by hand. The electrical static can kill the chips even without a power plug-in. Unpleasant electrical shock may also be felt. For laboratory use, please buy a Turnkey system.

Legal notices: All product information is believed to be accurate and is subject to change without notice. Information contained herein shall legally bind Agiltron only if it is specifically incorporated into the terms and conditions of a sales agreement. Some specific combinations of options may not be available. The user assumes all risks and liability whatsoever in connection with the use of a product or its application.

Rev 10/28/24

© Photonwares Corporation

P +1 781-935-1200

E sales@photonwares.com

W www.agiltron.com

Information contained herein is deemed to be reliable and accurate as of the issue date. Photonwares reserves the right to change the design or specifications at any time without notice. Agiltron is a registered trademark of Photonwares Corporation in the U.S. and other countries.

NanoSpeed™ Switchable Fiber Optical Splitter/Coupler

(1x2, 2x2, SM, PM, Bidirectional)



DATASHEET

Mechanical Dimensions (Unit: mm)



*Product dimensions may change without notice. This is sometimes required for non-standard specifications.

Driving Board Selection

Maximum Repetition Rate	Part Number (P/N)
100 kHz	SWDR-11a261111
500 kHz	SWDR-11a291111

* Note: For customers that prefer to design their own driving circuit, they are responsible for the optical performance. For more technical information, please contact us.

Operation Instruction

1. Plug in the accompanied power supply
2. Plug in a 0-5V control signal to the input SMA connector (golden color). One can use a DC power supply first, and then a function generator. The optical output will change from maximum to minimum or from minimum to maximum depending on which port is measured.
3. Do not adjust settings on the board


NanoSpeed™ Switchable Fiber Optical Splitter/Coupler

(1x2, 2x2, SM, PM, Bidirectional)



DATASHEET

Typical Speed Response Measurement



Optical: —
Electrical: —

Ordering Information (Part Number)

Prefix	Type	Wavelength	Repetition	Initial split ratio ^[1]	Switching split ratio ^[1]	Fiber Type	Fiber Cover	Fiber Length	Connector ^[2]	Optical Power
NSSS-	1x2 = A 2x2 = B	1060 = 1 L Band = 2 1310 = 3 1550 = 5 780 = 7 850 = 8 980 = 9 Special = 0	100kHz = 1 500kHz = 5 Special = 0	0:100 = A 10:90 = 1 20:80 = 2 30:70 = 3 40:60 = 4 50:50 = 5 60:40 = 6 70:30 = 7 80:20 = 8 90:10 = 9 Special = 0	100:0 = A 90:10 = 1 80:20 = 2 70:30 = 3 60:40 = 4 50:50 = 5 40:60 = 6 30:70 = 7 20:80 = 8 10:90 = 9 Special = 0	SMF-28 = 1 HI1060 = 2 PM1550 = 5 HI780 = 3 PM780 = 7 PM850 = 8 PM980 = 9 Special = 0	Bare fiber = 1 900um tube = 3 Special = 0	0.25m = 1 0.5m = 2 1.0 m = 3 Special = 0	None = 1 FC/PC = 2 FC/APC = 3 SC/PC = 4 SC/APC = 5 ST/PC = 6 LC/PC = 7 Duplex LC/PC = 8 LC/APC = 9 E2000 APC = A LC/UPC = U Special = 0	Regular = 1 1W = A 2W = B 5W = C 10W = D 20W = E

[1]. Initial and Switched splitting ratios could be combined in arbitrary

[2]. The default connector configuration uses fiber with 0.9 mm buffer protection. The connector cannot be installed directly onto bare fiber because the bare fiber is prone to damage during shipping. However, the connector can be assembled on bare fiber if a 3 cm protective loose tube is added for reinforcement. The customer may remove this protective tube after testing. The optical power handling of a standard connector is less than 0.5 W for SMF-28 fiber and decreases further for smaller-core fibers.

Note:

PM1550 fiber works well for 1310nm

Fiber Core Alignment

Note that the minimum attenuation for these devices depends on excellent core-to-core alignment when the connectors are mated. This is crucial for shorter wavelengths with smaller fiber core diameters that can increase the loss of many decibels above the specification if they are not perfectly aligned. Different vendors' connectors may not mate well with each other, especially for angled APC.

Fiber Cleanliness

Fibers with smaller core diameters (<5 µm) must be kept extremely clean, contamination at fiber-fiber interfaces, combined with the high optical power density, can lead to significant optical damage. This type of damage usually requires re-polishing or replacement of the connector.

Maximum Optical Input Power

Due to their small fiber core diameters for short wavelength and high photon energies, the damage thresholds for device is substantially reduced than the common 1550nm fiber. To avoid damage to the exposed fiber end faces and internal components, the optical input power should never exceed 20 mW for wavelengths shorter 650nm. We produce a special version to increase the how handling by expanding the core side at the fiber ends.

© Photonwares Corporation

+1 781-935-1200

sales@photonwares.com

www.agiltron.com

Information contained herein is deemed to be reliable and accurate as of the issue date. Photonwares reserves the right to change the design or specifications at any time without notice. Agiltron is a registered trademark of Photonwares Corporation in the U.S. and other countries.


NanoSpeed™ Switchable Fiber Optical Splitter/Coupler

(1x2, 2x2, SM, PM, Bidirectional)




DATASHEET

Optical Power Handling vs Wavelength For Single-Mode Fibers



Wavelength Bandwidth Measurement



NanoSpeed™ Switchable Fiber Optical Splitter/Coupler

(1x2, 2x2, SM, PM, Bidirectional)



DATASHEET

Q & A

Q: Does NS device drift over time and temperature?

A: NS devices are based on electro-optical crystal materials that can be influenced to a certain range by the environmental variations. The insertion loss of the device is only affected by the thermal expansion induced miss-alignment. For extended temperature operation, we offer special packaging to -40 -100 °C. The extinction or cross-talk value is affected by many EO material characters, including temperature-dependent birefringence, V_p , temperature gradient, optical power, at resonance points (electronic). However, the devices are designed to meet the minimum extinction/cross-talk stated on the spec sheets. It is important to avoid a temperature gradient along the device length.

Q: What is the actual applying voltage on the device?

A: 100 to 400V depending on the version.

Q: How does the device work?

A: NS devices are not based on Mach-Zander Interference, rather birefringence crystal's nature beam displacement, in which the crystal creates two different paths for beams with different polarization orientations.

Q: What is the limitation for faster operation?

A: NS devices have been tested to have an optical response of about 300 ps. However, practical implementation limits the response speeds. It is possible to achieve a much faster response when operated at partial extinction value. We also offer resonance devices over 20MHz with low electrical power consumption.

Operation Manual

1. Connect a control signal to the SMA connector on the PCB.
2. Attach the accompanied power supply (typically a wall-pluggable unit).
3. The device should then function properly.

Note: Do not alter device factory settings.