



PMS-L65

It has a linear guide motion system with high precision, high efficiency and smaller friction coefficient, which greatly improves the optical performance, accuracy, stability and service life of the lens.

6.5× Linear Zoom Lens Parameter Table										
Magnification Range		0.7×~4.5×								
Working Distance(mm)		87±2mm								
Magnification		0.7×	1.0×	1.5×	2.0×	2.5×	3.0×	3.5×	4.0×	4.5×
DOF(mm)		1.9	0.952	0.44	0.29	0.23	0.16	0.13	0.12	0.1
N.A.		0.03	0.042	0.06	0.07	0.07	0.085	0.085	0.085	0.085
F.No.		11.6	12.1	12.5	14.2	17.8	17.6	20.5	23.5	26.5
Resolution(μm)		11.18	7.99	5.59	4.79	4.79	3.95	3.95	3.95	3.95
TV Distortion		0.019%	0.035%	0.002%	0.003%	0.004%	0.001%	0.001%	0.002%	0.002%
FOV(mm)	2/3"	15.71×12.57×9.43	11.00×8.80×6.60	7.33×5.87×4.40	5.50×4.40×3.30	4.40×3.52×2.64	3.67×2.93×2.20	3.14×2.21×1.89	2.75×2.20×1.65	2.44×1.96×1.47
	1/2"	11.43×9.14×6.86	8.00×6.40×4.80	5.33×4.27×3.20	4.00×3.20×2.40	3.20×2.56×1.92	2.67×2.13×1.60	2.29×1.83×1.37	2.00×1.60×1.20	1.78×1.42×1.07
	1/3"	8.57×6.86×5.14	6.00×4.80×3.60	4.00×3.20×2.40	3.00×2.40×1.80	2.40×1.92×1.44	2.00×1.60×1.20	1.71×1.37×1.03	1.50×1.20×0.90	1.33×1.07×0.80
Max. Sensor Size		2/3"								
Mount		C-Mount								
Operating Environment		Temperature-10°C~+50°C; Humidity: 30-80% (no Condensation)								

PRODUCT ADVANTAGES

- Fast and accurate zoom;
- Use of navigation structure, eliminating the limitation of the number of times of zoom;
- High zoom ratio, optional zoom ratio 6.5X/7.5X/12.5X;
- Support 2/3" target surface, built-in double-guide structure of continuous zoom lens;
- High contrast, using the core adjustment method to solve the impact of the optical element centre offset on the imaging contrast.

APPLICATION FIELDS

Widely used in biology, electronics, semiconductor, machine vision and other high-precision industries.

